

Technical Data Sheet


PILL COUNTERTOP BASIN

What's in the box: 1x DC12051









Diagrams not to scale All dimensions in mm Tolerance of +/-5mm

Materials

Basin: Ceramic

**Dimensions are subject to change, customers are advised to measure actual product before commencing installation.

FAQs

Q: What is the maximum water depth of the basin?

Q: Can this basin be wall mounted?

Q: What are the taphole/ basin waste sizes?

Q: Where should the basin be located on the worktop?

Q: What ranges can this basin be used on?

Furniture units compatibility

A: Measurement not applicable. Since this basin does not have an overflow channel it should only be used with an open waste.

A. No.

A: All sizes are to British Standard - (BS EN 31)

- Diameter of the central tap hole = 35mm : +2/-1mm
- Bore of the waste outlet hole = 46mm : +2 / -3mm

A: We recommend it being centralised on the worktop left to right. Front to back should be set based on desired tap location and waste outlet.

Cadence					Compass		Acumen		
500	600	800	1000	1200	500	600	500	600	800
No	Yes	Yes	Yes	Yes	No	Yes	No	Yes	Yes

^{***} BASIN HAS NO OVERFLOW SO MUST BE USED WITH AN OPEN WASTE