Technical Data Sheet

Cohort Lever Tall Basin Mixer with Click Waste

TCL5009 (Stainless Steel)




FLOW RATE DATA IS TESTED UNDER LABORATORY CONDITIONS: ACTUAL FLOW RATE MAY VARY DEPENDING ON DOMESTIC SUPPLY AND ACCESSORIES





Dimensions

Diagrams not to scale. All dimensions in mm (tolerance of +/-5mm)



FAQs

What connections do the flexible hoses have? This tap uses flexible hoses with 1/2"BSP captive nut connections.

What size Pipework do i need? It is recommended to use 15mm with G1/2" plumbing fittings.

What is the recomended operating pressure? 0.5 BAR.

How do I care for the finish on this tap? We recommend using only a damp cloth and warm water. Do NOT use abrasive cleaning products or cleaning chemicals as this may damage the surface of the product.

What is the raw material for this product? This product is made from 316 grade stainless steel.

Is the supplied click waste suitable for use with a vessel basin? Yes, the waste can be used with vessel basins with and without an integrated overflow.